



Clear

Photopolymer Resin for Form 1+ and Form 2

FLGPCLO3 MATERIAL PROPERTIES

Prepared: 04/19/2016

To the best of our knowledge the information contained herein is accurate. However, Formlabs, Inc. makes no warranty, expressed or implied regarding the accuracy of these results to be obtained from the use thereof.

Formlabs Clear Resin produces strong plastic parts ideal for a wide variety of applications and is specifically designed to work with your Form 2 or Form 1+ 3D Printer. This material can be easily painted, and when the surface is finished or coated, produces a highly clear part. Upon post-cure, tensile strength and stiffness exceeds that of injection-molded or 3D-printed ABS.

The following material properties are comparable for all our Standard Resins, White, Grey, and Black.

	METRIC ¹		IMPERIAL ¹		METHOD
	Green ²	Postcured ³	Green ²	Postcured ³	
Tensile Properties					
Ultimate Tensile Strength	38 MPa	65 MPa	5510 psi	9380 psi	ASTM D 638-10
Young's Modulus	1.6 GPa	2.8 GPa	234 ksi	402 ksi	ASTM D 638-10
Elongation at Failure	12%	6.2%	12%	6.2%	ASTM D 638-10
Flexural Properties					
Flexural Modulus	1.25 GPa	2.2 GPa	181 ksi	320 ksi	ASTM C 790-10
Impact Properties					
Notched IZOD	16 J/m	25 J/m	0.3 ft-lbf/in	0.46 ft-lbf/in	ASTM D 256-10
Temperature Properties					
Heat deflection temp. @ 264 psi	42.7 °C	58.4 °C	108.9 °F	137.1 °F	ASTM D 648-07
Heat deflection temp. @ 66 psi	49.7 °C	73.1 °C	121.5 °F	163.6 °F	ASTM D 648-07

NOTES:

¹Material properties can vary with part geometry, print orientation, print settings and temperature.

²Data was obtained from green parts, printed using Form 2, 100 µm, Clear settings, without additional treatments.

³ Data was obtained from parts printed using Form 2, 100 µm, Clear settings and post-cured with 1.25 mW/cm² of 405 nm LED light at 60 °C for 60 minutes.

SOLVENT COMPATIBILITY

Percent weight gain over 24 hours for a printed and post-cured 1 x 1 x 1 cm cube immersed in respective solvent:

Mechanical Properties	24 HR WEIGHT GAIN (%)
Acetic Acid, 5 %	<1
Acetone	sample cracked
Isopropyl Alcohol	<1
Bleach, ~5 % NaOCl	<1
Butyl Acetate	<1
Diesel	<1
Diethyl glycol monomethyl ether	1.7
Hydraulic Oil	<1
Skydrol 5	1
Hydrogen Peroxide (3 %)	<1
Isooctane	<1
Mineral Oil, light	<1
Mineral Oil, heavy	<1
Salt Water (3.5 % NaCl)	<1
Sodium hydroxide (0.025 %, pH = 10)	<1
Water	<1
Xylene	<1
Strong Acid (HCl Conc)	distorted